

Catalog Number

47451-01-010

Adapter, for use with low to medium pressure HPLC. 1/4-28 female to 10-32 male connection, 0.40 mm / 0.016 bore size. PEEK. ARE-Applied Research brand. 10/PK.



Additional Info

This finger tightened adapter makes changing from a standard 1/4-28 threaded female port to a 10/32 female port very easy and convenient. This all-PEEK adapter has a standard male connector with a built-in ferrule with a "universal" pilot length.

- Maximum Temperature: 100°C
- Maximum Pressure: 8,000 psig.
- Click [HERE](#) for a bulk pricing inquiry.

The "flat" section on the knurled adapter allows to use a wrench for an extra 1/8 of clockwise turn for tighter sealing or a slight counterclockwise turn to help remove if a tight fitting is too hard for hand removal. The flat section can also be used to hold the adapter in place with a wrench while the male nut is tightened in the adapter.

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$597.06

Printed On 2024/05/19