

Catalog Number

58545-N47

Filters, Membrane, 47mm, 0.45um, Nylon. Round, AQ Brand. 100/PK.



Additional Info

These high flow, non media migrating, Nylon-66, Advanced Quality (AQ) Brand, Filter Discs can be used with the Mobile Phase Filter Degasser Assembly or any device when membrane filtration is desired.

Hydrophilic membranes with minimal extractables and absolute retention, they can be autoclaved at 121°C for 30 minutes or EO sterilization without damage to the integrity or performance of the filter.

- Diameter: 47mm
- Max Operating Temperature: 80°C
- Bubble Point: >32psi (2.25 kg/cm²)
- Water Flow Rate: >32ml/min/cm² @ 10 psi, 27°C
- Thickness: 150um +- 20um
- Extractables with WFI (water): Within USP Limits

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$0.00

Printed On 2024/05/20