


## Catalog Number

97041-11

**Septa, 22mm, Natural Silicone Rubber / White PTFE. Ultra Low Bleed.**  
For use in 24mm Caps, sold separately. BASIK Brand. 1000/CS.



### Additional Info

Silicone Rubber / PTFE Septa 2.5mm thick. This Septa is good for storage or EPA Testing due to the high purity of the rubber and PTFE. Temperature range from -60° to 200°C.

Use in screw caps that have 24mm or ND2 threads.. Supplied in a polyethylene Bags.

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$998.54**

Printed On 2024/05/20