

Catalog Number

07200-S

Window Maker, Polyimide Coating Remover, 110/120v for 2mm
Detection Windows for CE. MicroSolv Brand. 1 EA.



Additional Info

This Window Maker will precisely burn off polyimide from 365um OD Capillaries for Capillary Electrophoresis. This unit includes a replaceable [heating module](#) that will burn approximately, 2mm Detection Windows without causing any defects in the Fused Silica with sharp edges, for maximum UV or Fluorescence Detection. Other size heating modules are sold separately that can be used with it.

110/120V with a US type Plug and is Not CE Marked.

Easy to operate, this unit comes with an instruction manual to achieve Optimal Performance.

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$753.85

Printed On 2024/05/19