

Catalog Number

95020-55S-W

Caps, Headspace, Screw Top, with White Silicone Rubber / Blue PTFE Temperature Resistant Septa, fitted in Steel, Magnetic, Silver Caps with 8mm center holes. For use with 18mm Precision Thread Headspace



Additional Info

Silicone Rubber / Ultraclean PTFE Septa has a durometer of 55° Shore A (hardness) and is 1.5mm thick. Cap has ND18 Screw Threads. Recommended with CTC®, Agilent®, Perkin Elmer TurboMax® 16, 40 & 110 and other autosamplers.

Temperature resistant from -60C to 200C. Cap has ND18 Screw Threads.

Click [HERE](#) for case quantities.

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$314.71

Printed On 2024/05/19