


Catalog Number

95025-22

Septa, 17.5mm, Headspace, Transparent, Bluish Silicone Rubber / White PTFE. For use in 18mm Aluminum, Screw Caps, sold separately. MicroSolv Brand. 1000/CS.



Additional Info

Silicone Rubber / Ultra Clean PTFE, with Durometer of 45 Shore A, (hardness) and 1.3mm thick is good for sensitive analyses. The lower Durometer means that this is a softer Septa and therefore better for easier penetrations by autosampler needles.

Use in ND18, Precision Thread Screw Caps for Headspace autosamplers. Supplied in Polyethylene Bags.

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$1,741.13

Printed On 2024/05/19