

## Catalog Number

9509S-30C-K

**Caps, Screw Top**, with Silicone Rubber / PTFE, ultra-pure, Pre-Slit Septa, fitted in knurled, polypropylene, Black Caps. For use with 9-425mm thread, 12x32mm autosampler vials. AQR Brand. 100/PK.



### Additional Info

When highest purity in a Septa is required. No color added to the rubber or PTFE (Teflon) for improved purity these caps offer virtually no extractables including colors that can contaminate sensitive analyses.

Often chosen for LCMS, GCMS & LCMS/MS. These Caps can be used as replacement Caps in [RSA-Pro X Kits](#).

Pre-slit for easy penetration by autosampler needles and recommended for Waters® Alliance, Acquity™ and all other autosamplers that require Pre-Slit Septa.

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$55.51**

Printed On 2024/06/01